

# Driving decarbonization and digitalization. Together.



## Project Manager Automation

### Job description

For Semiconductor BE Wuxi lights out program, including streamline projects / automation projects / digitalization projects / synchronization projects.

In your new role you will:

- Responsible for the Wuxi site automation project, including AGV, AOI, autoloader & unloader, etc., to achieve high efficiency of the production line.
- Investigate opportunities and potentials within operations and drive the agreed initiatives towards a better setup with application of LEAN concept.
- Responsible for the customer's voice communication, including but not limited to the internal & external customer's requirement.
- Manage the progress of the project and key milestones.
- Responsible for capital application with attractive ROI. Responsible for project cost management, risk control, etc.
- Responsible for supplier selection.
- Responsible for managing the progress of automation projects and problem solving.

### Profile

You are best equipped for this task if you have:

- Hold bachelor degree or above.
- Hold a degree within Industrial Engineering or Supply Chain in combination with a previous role as PM. In addition you are certified in PMI (Project Management Institute) or same level certification. Change management experience is seen as a strong merit.
- Have rich experience from Global Project Management working across countries and cultures as your main customers will be from Asia and Europe, semiconductor or manufacturing is preferred.
- Have more than 3x automation projects implementation experience as PM.
- Familiar with I40 layers, including ERP, MES, WMS etc.
- Solid interpersonal communication and influencing skills.
- Target oriented, strong problem solving skills, team player, sense of ownership.

### Benefits

### At a glance

Location: **Wuxi, (China)**  
Job ID: **HRC0774863**  
Start date: **May 21, 2024**  
Entry level: **5+ years**  
Type: **Full time**  
Contract: **Permanent**

Apply to this position online by following the URL and entering the Job ID in our job search. Alternatively, you can also scan the QR code with your smartphone:

Job ID: **HRC0774863**  
[www.infineon.com/jobs](http://www.infineon.com/jobs)



### Contact

[sarah.yu@infineon.com](mailto:sarah.yu@infineon.com)



- **Wuxi** : Möglichkeit für Coaching, Mentoring & Netzwerken; Trainingsangebot & strukturierte Entwicklungsplanung; Möglichkeit zur internationalen Entsendung; Verschiedene Karrierepfade: Project Management, Technical Ladder, Management & Individual Contributor; Flexible Arbeitszeit: Vertrauensgleitzeit; Medical coverage; Sozialberatung & Betriebsarzt; Gesundheits- & Vorsorgeprogramme; Kantine; Lohnfortzahlung im Krankheitsfall; Arbeitgeberfinanzierte betriebliche Altersvorsorge; Erfolgsbonus; Vergünstigtes Jobticket

## Why Us

### **Driving decarbonization and digitalization. Together.**

Infineon designs, develops, manufactures, and markets a broad range of semiconductors and semiconductor-based solutions, focusing on key markets in the automotive, industrial, and consumer sectors. Its products range from standard components to special components for digital, analog, and mixed-signal applications to customer-specific solutions together with the appropriate software.

### **We are on a journey to create the best Infineon for everyone.**

This means we embrace diversity and inclusion and welcome everyone for who they are. At Infineon, we offer a working environment characterized by trust, openness, respect and tolerance and are committed to give all applicants and employees equal opportunities. We base our recruiting decisions on the applicant´s experience and skills.

We look forward to receiving your resume, even if you do not entirely meet all the requirements of the job posting.

Please let your recruiter know if they need to pay special attention to something in order to enable your participation in the interview process.

[Click here](#) for more information about Diversity & Inclusion at Infineon.

