


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	2.46
A1	0.35	-	-
D	27 BSC		
E	27 BSC		
D2	24 BSC		
E2	24 BSC		
$\text{Ø}b$	0.6	0.75	0.9
eD	1.27 BSC		
eE	1.27 BSC		
SD / SE	0.635		