



1) Does not include plastic shall not exceed 0.15mm max. per side.

2) Dambar protrusion shall be maximum 0.1mm per side.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ±0.1;±1°30'