


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.15
b	0.15	-	0.27
c	0.09	-	0.2
D	16 BSC		
D1	14 BSC		
e	0.5 BSC		
E	16 BSC		
E1	14 BSC		
L	0.45	0.6	0.75

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]