



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.2
b	0.25	0.35	0.45
c	0.107	-	0.177
D	13.6 BSC		
D1	10 BSC		
e	0.8 BSC		
E	13.6 BSC		
E1	10 BSC		
L	0.8	1	1.2
θ	0°	-	8°

1) Dimensions D1 and E1 do not include mold protrusion. allowable protrusion is 0.25mm per side.

2) Dimension b does not include dambar protrusion. the dambar protrusion(s) shall not cause the lead width to exceed b maximum by more than 0.08mm.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []