



All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.15	-	-
D	10 BSC		
E	10 BSC		
Øb	0.21	0.26	0.31
eD	0.4 BSC		
eE	0.4 BSC		