


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.18	-	-
A2	0.62	-	0.74
D	8 BSC		
E	8 BSC		
$\varnothing b$	0.25	0.3	0.35
eE/eD	0.5 BSC		
SE/SD	0.25 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing methods per ASME Y14.5M-1994.