


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.635
A1	0.165	0.19	0.215
A2	0.4 BSC.		
A3	0.07 BSC.		
A4	0.025 BSC.		
D	3.15 BSC.		
E	3.65 BSC.		
$\text{Ø}b$	0.24	0.27	0.3
eD	0.4 BSC.		
eE	0.4 BSC.		
SD/SE	0 / 0.2		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []