# SiC

Silicon Carbide Diode

# 5th Generation thinQ!™

650V SiC Schottky Diode

# IDW16G65C5

## Final Datasheet

Rev. 2.2, 2013-01-15

Power Management & Multimarket

# 5th Generation thinQ!™ SiC Schottky Diode IDW16G65C5







## 1 Description

ThinQ!™ Generation 5 represents Infineon leading edge technology for the SiC Schottky Barrier diodes. Thanks to the more compact design and thin-wafer technology, the new family of products shows improved efficiency over all load conditions, resulting from both the improved thermal characteristics and a lower figure of merit (Qc x Vf).

The new thinQ!™ Generation 5 has been designed to complement our 650V CoolMOS™ families: this ensures meeting the most stringent application requirements in this voltage range.

### Features

- Revolutionary semiconductor material - Silicon Carbide
- Benchmark switching behavior
- No reverse recovery/ No forward recovery
- Temperature independent switching behavior
- High surge current capability
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC[1)] for target applications
- Breakdown voltage tested at 35 mA[2)]
- Optimized for high temperature operation

### Benefits

- System efficiency improvement over Si diodes
- System cost / size savings due to reduced cooling requirements
- Enabling higher frequency / increased power density solutions
- Higher system reliability due to lower operating temperatures
- Reduced EMI

### Applications

- Switch mode power supply
- Power factor correction
- Solar inverter
- Uninterruptible power supply

**Table 1 Key Performance Parameters**

| Parameter | Value | Unit |
|---|---|---|
| $V_{DC}$ | 650 | V |
| $Q_C$; $V_R$=400V | 23 | nC |
| $E_C$; $V_R$=400V | 5.3 | µJ |
| $I_F$ @ $T_C$ < 120°C | 16 | A |

**Table 2 Pin Definition**

| Pin 1 | Pin 2 | Pin 3 |
|---|---|---|
| n.c. | C | A |

| Type / ordering Code | Package | Marking | Related links |
|---|---|---|---|
| IDW16G65C5 | PG-TO247-3 | D1665C5 | www.infineon.com/sic |

1) J-STD20 and JESD22

2) All devices tested under avalanche conditions for a time periode of 10ms

# Table of Contents

1 Description ..... 2
2 Maximum ratings ..... 4
3 Thermal characteristics ..... 4
4 Electrical characteristics ..... 5
5 Electrical characteristics diagrams ..... 6
6 Simplified Forward Characteristics Model ..... 8
7 Package outlines ..... 9
8 Revision History ..... 10

## 2 Maximum ratings

**Table 3 Maximum ratings**

| Parameter | Symbol | Values | | | Unit | Note/Test Condition |
|---|---|---|---|---|---|---|
| | | Min. | Typ. | Max. | | |
| Continuous forward current | $I_F$ | – | – | 16 | A | $T_C$ < 120°C, D=1 |
| Surge non-repetitive forward current, sine halfwave | $I_{F,SM}$ | – | – | 95 | | $T_C$ = 25°C, $t_p$=10 ms |
| | | – | – | 74 | | $T_C$ = 150°C, $t_p$=10 ms |
| Non-repetitive peak forward current | $I_{F,max}$ | – | – | 637 | | $T_C$ = 25°C, $t_p$=10 µs |
| i²t value | $\int i^2dt$ | – | – | 45 | A²s | $T_C$ = 25°C, $t_p$=10 ms |
| | | – | – | 28 | | $T_C$ = 150°C, $t_p$=10 ms |
| Repetitive peak reverse voltage | $V_{RRM}$ | – | – | 650 | V | |
| Diode dv/dt ruggedness | $dv/dt$ | – | – | 100 | V/ns | $V_R$=0..480 V |
| Power dissipation | $P_{tot}$ | – | – | 94 | W | $T_C$ = 25°C |
| Operating and storage temperature | $T_j$;$T_{stg}$ | -55 | – | 175 | °C | |
| Mounting torque | | – | 50 | 70 | Ncm | M3 and M4 screws |

## 3 Thermal characteristics

**Table 4 Thermal characteristics TO-247-3**

| Parameter | Symbol | Values | | | Unit | Note/Test Condition |
|---|---|---|---|---|---|---|
| | | Min. | Typ. | Max. | | |
| Thermal resistance, junction-case | $R_{thJC}$ | – | 1.2 | 1.6 | K/W | |
| Thermal resistance, junction-ambient | $R_{thJA}$ | – | – | 62 | | leaded |
| Soldering temperature, wavesoldering only allowed at leads | $T_{sold}$ | – | – | 260 | °C | 1.6mm (0.063 in.) from case for 10 s |

# 4 Electrical characteristics

**Table 5 Static characteristics**

| Parameter | Symbol | Values | | | Unit | Note/Test Condition |
|---|---|---|---|---|---|---|
| | | Min. | Typ. | Max. | | |
| DC blocking voltage | $V_{DC}$ | 650 | – | – | V | $I_R$= 0.2 mA, $T_j$ = 25°C |
| Diode forward voltage | $V_F$ | – | 1.5 | 1.7 | | $I_F$= 16 A, $T_j$=25°C |
| | | – | 1.8 | 2.1 | | $I_F$= 16 A, $T_j$=150°C |
| Reverse current | $I_R$ | – | 0.8 | 200 | µA | $V_R$=650 V, $T_j$=25°C |
| | | – | 0.2 | 71 | | $V_R$=600 V, $T_j$=25°C |
| | | – | 3.2 | 1400 | | $V_R$=650 V, $T_j$=150°C |

**Table 6 AC characteristics**

| Parameter | Symbol | Values | | | Unit | Note/Test Condition |
|---|---|---|---|---|---|---|
| | | Min. | Typ. | Max. | | |
| Total capacitive charge | $Q_c$ | – | 23 | | nC | $V_R$=400 V, *di/dt*=200A/µs, $I_F \le I_{F,MAX}$, $T_j$=150°C. |
| Total Capacitance | $C$ | – | 470 | – | pF | $V_R$=1 V, *f*=1 MHz |
| | | – | 61 | – | | $V_R$=300 V, *f*=1 MHz |
| | | – | 60 | – | | $V_R$=600 V, *f*=1 MHz |

# 5 Electrical characteristics diagrams

**Table 7**

| Power dissipation | Diode forward Current |
|---|---|
|  |  |
| $P_{tot}$=f($T_C$); $R_{thJC,max}$ | $I_F$=f($T_C$); $T_j$≤175°C; $R_{thJC,max}$; parameter $D$=duty cycle |

**Table 8**

| Typical forward characteristics | Typical forward characteristics in surge current |
|---|---|
|  |  |
| $I_F$=f($V_F$); $t_p$=200 µs; parameter: $T_j$ | $I_F$=f($V_F$); $t_p$=200 µs; parameter: $T_j$ |

**Table 9**

| Typ. capacitance charge vs. current slope[1)] | Typ. reverse current vs. reverse voltage |
|---|---|
|  |  |
| $Q_C$=f(di$_F$/dt); $T_j$=150°C; $V_R$=400 V; $I_F \leq I_{F,max}$ | $I_R$=f($V_R$); parameter: $T_j$; |

1) Only capacitive charge, guaranteed by design.

**Table 10**

| Max. transient thermal impedance | Typ. capacitance vs. reverse voltage |
|---|---|
|  |  |
| $Z_{th,jc}$=f($t_P$); parameter: D=$t_P$/$T$; | $C$=f($V_R$); $T_j$=25°C; $f$=1 MHz |

**Table 11**

| Typ. capacitance stored energy |
|---|
|  |
| $E_C$=f($V_R$) |

## 6 Simplified Forward Characteristics Model

**Table 12**

| Equivalent forward current curve | Mathematical Equation |
|---|---|
|  | $V_F = V_{TH} + R_{DIFF} \cdot I_F$<br>$V_{TH}(T_j) = -0.001 \cdot T_j + 1.04$ [V]<br>$R_{DIFF}(T_j) = 8 \cdot 10^{-7} \cdot T_j^2 + 8 \cdot 10^{-5} \cdot T_j + 0.029$ [Ω] |
| $V_F$=f($I_F$) | $T_j$ in °C; -55°C < $T_j$ < 175°C; $I_F$ < 32 A |

# 7 Package outlines




| DIM | MILLIMETERS | | INCHES | |
|---|---|---|---|---|
| | MIN | MAX | MIN | MAX |
| A | 4.83 | 5.21 | 0.190 | 0.205 |
| A1 | 2.27 | 2.54 | 0.089 | 0.100 |
| A2 | 1.85 | 2.16 | 0.073 | 0.085 |
| b | 1.07 | 1.33 | 0.042 | 0.052 |
| b1 | 1.90 | 2.41 | 0.075 | 0.095 |
| b2 | 1.90 | 2.16 | 0.075 | 0.085 |
| b3 | 2.87 | 3.38 | 0.113 | 0.133 |
| b4 | 2.87 | 3.13 | 0.113 | 0.123 |
| c | 0.55 | 0.68 | 0.022 | 0.027 |
| D | 20.80 | 21.10 | 0.819 | 0.831 |
| D1 | 16.25 | 17.65 | 0.640 | 0.695 |
| D2 | 0.95 | 1.35 | 0.037 | 0.053 |
| E | 15.70 | 16.13 | 0.618 | 0.635 |
| E1 | 13.10 | 14.15 | 0.516 | 0.557 |
| E2 | 3.68 | 5.10 | 0.145 | 0.201 |
| E3 | 1.00 | 2.60 | 0.039 | 0.102 |
| e | 5.44 (BSC) | | 0.214 (BSC) | |
| N | 3 | | 3 | |
| L | 19.80 | 20.32 | 0.780 | 0.800 |
| L1 | 4.10 | 4.47 | 0.161 | 0.176 |
| øP | 3.50 | 3.70 | 0.138 | 0.146 |
| Q | 5.49 | 6.00 | 0.216 | 0.236 |
| S | 6.04 | 6.30 | 0.238 | 0.248 |

DOCUMENT NO.
Z8B00003327

SCALE
0 5 5 7.5mm

EUROPEAN PROJECTION

ISSUE DATE
09-07-2010

REVISION
05

**Figure 1 Outlines TO-247, dimensions in mm/inches**

# 8 Revision History

**5th Generation thinQ!™ SiC Schottky Diode**

**Revision History: 2013-01-15, Rev. 2.2**

**Previous Revision:**

| Revision | Subjects (major changes since last version) |
|---|---|
| 2.0 | Release of the final datasheet. |
| 2.1 | Reverse current values, maximum diode forward voltage. |
| 2.2 | Reverse current values, tested avalanche current, simplified calculation model |

**We Listen to Your Comments**
Any information within this document that you feel is wrong, unclear or missing at all?
Your feedback will help us to continuously improve the quality of this document.
Please send your proposal (including a reference to this document) to: **erratum@infineon.com**

Edition 2013-01-15
Published by
Infineon Technologies AG
81726 Munich, Germany
© 2013 Infineon Technologies AG
All Rights Reserved.

**Legal Disclaimer**
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

**Information**
For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (**www.infineon.com**).

**Warnings**
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

w w w . i n f i n e o n . c o m

Published by Infineon Technologies AG