

USB-C charger & adapter board selection guide

Multi-port solutions



Power rating [W]	45	65	65	100
Name	VD_USB_PAG_45W_COOLGAN	VD_USB_PAG_65W_DUAL	REF_65W_2C_GAN_PAG1	REF_100W_2C_SSFB_PAG1
Topology	QR flyback	QR flyback	QR flyback + buck converters	Single-stage PFC flyback + buck converters
Primary start-up controller	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P
Synchronous rectification controller	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S
Protocol controller	EZ-PD™ CCG7DC	EZ-PD™ CCG7DC	EZ-PD™ CCG7DC	EZ-PD™ CCG7DC
High-voltage PWM switch	CoolMOS™	CoolMOS™	CoolGaN™	CoolMOS™
Medium-voltage SR switch	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™
V _{BUS} switch (load switch)	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™
Buck switch (dual-port only)	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™
Uncased size [mm x mm x mm]	63 x 32 x 25	51 x 51 x 29	55 x 27 x 33	60 x 60 x 28
Uncased power density [W/in ³]	14.6	14.1	21.34	16.25
Single port full-load efficiency (%) @ 115V _{AC} /230V _{AC}	(20 V/2.25 A = 45 W) 91.09 %/90.9 %	(20 V/3.25 A = 65 W) 90.55 %/91.01 %	(20 V/3.25 A = 65 W) 92.9 %/93.15 %	(20 V/5 A = 100 W) 87.25 %/89.09 %
Dual-port full-load efficiency (%) @ 115 V _{AC} /230 V _{AC}	(9 V/2.5 A + 9 V 2.5 A = 45 W) 88.1 %/87.025 %	(9 V/2.22 A + 20 V 2.25 A = 65 W) 89.72 %/89.95 %	(9 V/2.22 A + 20 V 2.25 A = 65 W) 92.1 %/92.58 %	(20 V/2.5 A + 20 V/2.5 A = 100 W) 86.5 %/88.5 %
CoC tier 2 & DoE level VI compliance	✓	✓	✓	✓
Standby power @ 230 V _{AC} [mW]	52	48	51	43
Feedback loop	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer
Programmable USB-PD protocol functionality	✓	✓	✓	✓
USB-PD PPS feature	✓	✓	✓	✓

For more information, please visit:

www.infineon.com/USB-PD

USB-C charger & adapter board selection guide

Single-port solutions



Power rating [W]	18	20	33	45	65	65	65
Name	VD_USB_PAG_18W_ADAPTER	VD_USB_PAG_20W_ADAPTER	VD_USB_PAG_33W_ADAPTER	VD_USB_PAG_45W_COOLGAN	VD_USB_PAG_65W_ADAPTER	VD_USB_PAG_65W_COOLGAN	DEMO_XDPS2201_65W1
Topology	QR flyback	QR flyback	QR flyback	QR flyback	QR flyback	QR flyback	Hybrid flyback
Primary start-up controller	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P	EZ-PD™ PAG1P	XDP™ XDPS2201
Synchronous rectification controller	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S	EZ-PD™ PAG1S	3rd party
Protocol controller							EZ-PD™ CCG3PA
High-voltage PWM switch	CoolMOS™	CoolMOS™	CoolMOS™	CoolGaN™	CoolMOS™	CoolGaN™	CoolMOS™
Medium-voltage SR switch	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™
V _{BUS} switch (load switch)	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™	OptiMOS™
Uncased size in [mm x mm x mm]	55 x 36 x 21	55 x 36 x 21	33 x 36 x 23	39 x 35 x 30	52 x 42 x 22	52 x 42 x 22	37 x 43 x 19
Uncased power density [W/in ³]	7.8	7.8	7.76	17.8	22.16	22.16	31
Full-load efficiency (%) @ 115 V _{AC} /230 V _{AC}	(11 V/1.64 A = 18 W) 89.23 %/89.1 %	(11 V/2.2 A = 20 W) 89 %/88.6 %	(11 V/3 A = 33 W) 90.54 %/90.19 %	(20 V/2.25 A = 45 W) 91.85 %/91.15 %	20 V/3.25 A 90.29 %/90.99 %	20 V/3.25 A 91.09 %/91.71 %	20 V/3.25 A 93.5 %/93.8 %
CoC tier 2 & DoE level VI compliance	✓	✓	✓	✓	✓	✓	✓
Standby power @ 230 V _{AC} [mW]	23	26	25	28	43	43	60
Feedback loop	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer	Pulse edge transformer	Opto coupler
Programmable USB-PD protocol functionality	✓	✓	✓	✓	✓	✓	✓
USB-PD PPS feature	✓	✓	✓	✓	✓	✓	✓

USB-C charger & adapter board selection guide

Single-port solutions



Power rating [W]	140	240
Name	REF_XDPS2221_140W1	EVAL_XDPS2222_240W1
Topology	Hybrid flyback	Hybrid flyback
Primary start-up controller	XDP™ XDPS2221	XDP™ XDPS2222
Synchronous rectification controller	3rd party	3rd party
Protocol controller	EZ-PD™ CCG3PA	EZ-PD™ CCG3PA
High-voltage PWM switch	CoolGaN™	CoolGaN™
Medium-voltage SR switch	OptiMOS™	OptiMOS™
V _{BUS} switch (load switch)	HEXFET	HEXFET
Uncased size in [mm x mm x mm]	109.5 x 38.5 x 24	200 x 65 x 24
Uncased power density [W/in ³]	22.67	12.7
Full-load efficiency (%) @ 115 V _{AC} /230 V _{AC}	28 V/5 A, 93.51 %/94.92 %	48 V/5 A = 240 W, 93.01 %/94.92 %
CoC tier 2 & DoE level VI compliance	✓	✓
Standby power @ 230 V _{AC} [mW]	49.08 (without EPR board)	79
Feedback loop	Opto coupler	Opto coupler
Programmable USB-PD protocol functionality	✓	✓
USB-PD PPS feature	✓	✓



www.infineon.com

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2023 Infineon Technologies AG
All rights reserved.

Public

Date: 07 / 2023

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.