




SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	1.65	-	1.75
A3	0.7 REF		
D	5 BSC		
E	7 BSC		
bD	1		
bE	1.4		
LD	1.18		
LE	1.28		
K	0.13		
e	2.54 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []