








SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	2.9
A1	0.17	0.2	0.23
A2	0.55 BSC		
D	10.3	10.45	10.6
D1	9.84	10.04	10.24
E	10.11	10.26	10.41
E1	7.3	7.45	7.6
E2	6.84	7.04	7.24
E3	4.7 BSC		
E4	9 BSC		
b	0.37	0.42	0.47
b1	0.81	0.94	1.07
L	1.2 BSC		
L1	1 BSC		
e	1.14	1.27	1.4

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []