

Product	Product category	Magnet	Material	Shape	Diameter	Height	Direction of Magnetisation	Standard Grade	Residual magnetism Br	Coercive field strength bHc	Max working temperature	Where to find and buy, link to
TLE4997	Linear Hall	FE-S-05-05	Ferrite	Disc	5mm	5mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLE4998	Linear Hall	FE-S-05-05	Ferrite	Disc	5mm	5mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLE4997	Linear Hall	S-05-05-N	NdFeB	Disc	5mm	5mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE4998	Linear Hall	S-05-05-N	NdFeB	Disc	5mm	5mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B6	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B7	3D Hall sensor	S-02-04-N	NdFeB	Rod	2 mm	4 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B8	3D Hall sensor	S-04-02-N	NdFeB	Disc	4 mm	2 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B9	3D Hall sensor	S-04-10-DN	NdFeB	Rod	4 mm	10 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B10	3D Hall sensor	S-02-02-N	NdFeB	Disc	2 mm	2 mm	Axial	N48	1.37-1.42 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B11	3D Hall sensor	S-04-04-N	NdFeB	Disc	4 mm	4 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B12	3D Hall sensor	S-04-02-N	NdFeB	Disc	4 mm	2 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B13	3D Hall sensor	FE-S-05-05	Ferrite	Disc	5 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLV493D-A1B14	3D Hall sensor	FE-S-10-05	Ferrite	Disc	10 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLV493D-A1B15	3D Hall sensor	FE-S-10-05	Ferrite	Disc	10 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLV493D-A1B16	3D Hall sensor	S-01-01-N	NdFeB	Disc	1 mm	1 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B17	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10 mm	5 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B18	3D Hall sensor	Q-19-13-06-LN	NdFeB	Cuboid	19.05 x 12.7 x 6.35 mm	-	Axial	N42	1.29-1.32 T	860-955 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B19	3D Hall sensor	Q-05-2.5-02-HN	NdFeB	Cuboid	5 x 2.5 x 2 mm	-	Axial	44H	1.32-1.36 T	860-1035 kA/m	120 degree	<a href="#">direct link</a>
TLV493D-A1B20	3D Hall sensor	S-04-10-DN	NdFeB	Rod	4 mm	10 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLV493D-A1B21	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10 mm	5 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-02-04-N	NdFeB	Rod	2 mm	4 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-04-02-N	NdFeB	Disc	4 mm	2 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-04-10-DN	NdFeB	Rod	4 mm	10 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-02-02-N	NdFeB	Disc	2 mm	2 mm	Axial	N48	1.37-1.42 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-04-04-N	NdFeB	Disc	4 mm	4 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-04-02-N	NdFeB	Disc	4 mm	2 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	FE-S-05-05	Ferrite	Disc	5 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	FE-S-10-05	Ferrite	Disc	10 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	FE-S-10-05	Ferrite	Disc	10 mm	5 mm	Axial	Y35	0.40-0.41 T	175-195 kA/m	250 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-01-01-N	NdFeB	Disc	1 mm	1 mm	Axial	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10 mm	5 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	Q-19-13-06-LN	NdFeB	Cuboid	19.05 x 12.7 x 6.35 mm	-	Axial	N42	1.29-1.32 T	860-955 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	Q-05-2.5-02-HN	NdFeB	Cuboid	5 x 2.5 x 2 mm	-	Axial	44H	1.32-1.36 T	860-1035 kA/m	120 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-04-10-DN	NdFeB	Rod	4 mm	10 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE493D-xx	3D Hall sensor	S-10-05-DN	NdFeB	Disc	10 mm	5 mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5309D	GMR & AMR Angle sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5009	GMR Angle sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	SM-10x05-N-D	Neodym	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	SM-10x05-N-D	Neodym	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	SD-10x5-NI-N45	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	SD-10x5-NI-N45	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5012 xx	GMR Angle sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	SD-6x2.5-NI-N35SH	NdFeB	Disc	6mm	2,5mm	Diametral	N35SH	1.17-1.22 T	≥ 876 kA/m	150 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	SM-10x05-N-D	Neodym	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	S-10-05-DN	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	SM-10x05-N-D	Neodym	Disc	10mm	5mm	Diametral	N45	1.32-1.37 T	860-995 kA/m	80 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	SD-10x5-NI-N45	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE5014 xx	GMR Angle sensor	SD-10x5-NI-N45	NdFeB	Disc	10mm	5mm	Diametral	N45			80 degree	<a href="#">direct link</a>
TLE4922	Speed sensor	BMHFa-23/22 K	Ferrite	Disc					0.345/0.365 T	202/220 kA/m	250 degree	<a href="#">direct link</a>