






SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.16	-	-
A2	-	-	0.81
D	8 BSC		
E	6 BSC		
Øb	0.25	0.3	0.35
eE	0.75 BSC		
eD	0.75 BSC		
SD	0.375 BSC		
SE	0.375 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing methods per ASME Y14.5M-2009.