







SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	1.75
A1	0.1	-	0.25
A2	1.25	-	-
b	0.3	-	0.45
D	4.9 BSC		
E	6 BSC		
E1	3.9 BSC		
e	1 BSC		
L	0.4	-	1.27
h	0.25	-	0.5
θ°	0	-	8

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []