


- 1) Does not include plastic or metal protrusion of 0.15 max. per side
 - 2) Lead width can be 0.61max in dambar area
 - 3) The chamfer feature is optional, in addition to pin 1 index marking
- All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Drawing according to ISO 8015 general tolerances ± 0.05 ; $\pm 30^\circ$