



TOP VIEW



BOTTOM VIEW



PIN 1


INDEX MARKING

1.27

0.4 ± 0.13

$\varnothing 0.25 \text{ (M) A}$

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

1) Does not include plastic or metal protrusion of 0.15 mm Max. per side