






SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.8
A1	0.4	-	-
D	18 BSC		
E	14 BSC		
Øb	0.5	0.6	0.7
eD	1 BSC		
eE	1 BSC		
SD	0.5 BSC		
SE	0.5 BSC		

All dimensions are in units mm

Dimensioning and Tolerancing methods per ASME Y14.5M-1994.

The drawing is in compliance with ISO 128-30, Projection Method 1 []