


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.35
A1	0.15	0.25	0.35
D	7 BSC		
E	7 BSC		
$\phi b$	0.2	0.3	0.4
eD	0.5 BSC		
eE	0.5 BSC		