






Bottom view



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.3
A1	0.15	0.25	0.35
D	6 BSC		
E	6 BSC		
Øb	0.27	0.32	0.37
eD	0.5 BSC		
eE	0.5 BSC		