






1) Exclude mold flash

2) Removal on mold gate, intrusion 0.1mm
protrusion 0.1mm

All metal surfaces are plated except area of cut.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0.1 / 1^\circ 30'$