


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.2
A1	0.15	-	-
D	10 BSC		
E	10 BSC		
Øb	0.25	0.3	0.35
eD	0.8 BSC		
eE	0.8 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []