



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	1.1
A1	0.25	-	-
D	8 BSC		
E	8 BSC		
Øb	0.35	0.4	0.45
eD	0.8 BSC		
eE	0.8 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]