


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.6
A1	0.05	-	0.15
A2	1.35	1.4	1.45
D	15.8	16	16.2
D1	13.9	14	14.1
E	21.8	22	22.2
E1	19.9	20	20.1
θ	0°	-	7°
c	-	-	0.2
b	0.22	0.3	0.38
L	0.45	0.6	0.75
e	0.65 TYP		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []