



Bottom view



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.05	-	0.15
D	18 BSC		
D1	16 BSC		
D2	5.8 REF		
D3	4.6 REF		
E	18 BSC		
E1	16 BSC		
E2	5.8 REF		
E3	4.6 REF		
$\theta$	0°	4°	8°
b	0.13	0.18	0.23
L	0.45	0.6	0.75
e	0.4 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]