








- 1) Does not include plastic or metal protrusion of 0.15 mm max. per side
 2) Dambar protrusion shall be maximum 0.1 mm total in excess of lead width.
 All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Drawing according to ISO 8015, general tolerances ± 0.05 ; $\pm 1^\circ 30'$