



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	0.8 BSC.		
N	8		
L	0.35	0.4	0.45
b	0.25	0.3	0.35
D2	2.2	2.3	2.4
E2	2.9	3	3.1
D	4 BSC		
E	4 BSC		
A	0.5	0.55	0.6
A1	0	0.035	0.05
A3	0.152 REF		
K	0.2	-	-

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []