






SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	0.78	0.88	0.98
A1	0.11	0.16	0.21
D	9.9	10	10.1
E	9.9	10	10.1
Øb	0.2	0.25	0.3
e	0.4 BSC		
S	0.19 REF		
M	0.53 REF		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []