


SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.97
A1	0.11	-	-
D	9 BSC		
E	9 BSC		
Øb	0.2	0.25	0.3
eD	0.8 BSC		
eE	0.8 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []