




SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.60
A1	0.00	-	0.05
A3 (Option 1)	0.152 REF		
A3 (Option 2)	0.127 REF		
b	0.18	0.25	0.30
D	4.00 BSC		
D2	2.65	2.75	2.85
E	4.00 BSC		
E2	2.65	2.75	2.85
L	0.30	0.40	0.50
e	0.50 BSC		

Dimensioning & tolerances conform to ASME Y14.5M. -1994.

Package warpage max 0.08 mm.

Index feature can either be an option 1 : "mouse bite" or option 2 : chamfer.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []