



Bottom view



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	0.65 BSC		
L	0.3	0.4	0.5
L1	0.35	0.45	0.55
b	0.25	0.3	0.35
D	3.18	3.23	3.28
E	3.23	3.28	3.33
A	0.45	0.50	0.55
A1	0	-	0.05

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []