






All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.7
A1	0.16	-	0.26
D	9.26 BSC		
E	8.87 BSC		
N	73		
Øb	0.27	-	0.37
eD	0.5 BSC		
eE	0.5 BSC		