



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.55
A1	0.16	-	-
D	2.51 BSC		
E	2.77 BSC		
D1	2.00 BSC		
E1	2.00 BSC		
Øb	0.20	0.25	0.30
eD	0.40 BSC		
eE	0.40 BSC		
SD	0.225 BSC		
SE	0.045 BSC		
f1	0.23 BSC		
f2	0.54 BSC		
f3	0.28 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []