






SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.55
A1	0.16	-	-
D	4.52 BSC		
E	2.92 BSC		
Øb	0.2	0.25	0.3
eD	0.4 BSC		
eE	0.4 BSC		

All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []