






SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.635
A1	0.165	0.19	0.215
A2	0.4 BSC		
A3	0.07 BSC		
A4	0.025 BSC		
D	4.38 BSC		
E	4.38 BSC		
Øb	0.24	0.27	0.3
eD	0.4 BSC		
eE	0.4 BSC		
SD/SE	0.2		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.