







SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.69
A1	0.21	0.24	0.27
A2	0.4 BSC		
A3	0.07 BSC		
A4	0.025 BSC		
D	3.6 BSC		
E	4.1 BSC		
Øb	0.285	0.315	0.345
eD	0.5 BSC		
eE	0.5 BSC		
SD	0		
SE	0.25 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.