


| SYMBOL | DIMENSIONS | | |
|-------------|------------|-------|-------|
| | MIN. | NOM. | MAX. |
| A | - | - | 0.42 |
| A1 | 0.089 | 0.099 | 0.109 |
| D | 1.447 | 1.472 | 1.497 |
| E | 1.554 | 1.579 | 1.604 |
| $\text{Ø}b$ | 0.17 | 0.20 | 0.23 |
| eD | 0.35 BSC | | |
| eE | 0.35 BSC | | |
| SD | 0.175 BSC | | |
| SE | 0.175 BSC | | |

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []