


### Bottom view



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.33
A1	0.081	-	-
D	3.676 BSC		
E	3.19 BSC		
∅b	0.1035	0.115	0.1265
eD	0.303 BSC		
eE	0.35 BSC		
SD	0.00 BSC		
SE	0.00 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]