



# PQFN 5x6 Outline "C" Package Details



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.0315	.0394	0.800	1.000
A1	.0000	.0020	0.000	0.050
b	.0098	.0138	0.250	0.350
b1	.0079	.0118	0.200	0.300
b2	.0138	.0177	0.350	0.450
c	.0080	REF.	0.203	REF.
D	.2362	BASIC	6.000	BASIC
E	.1969	BASIC	5.000	BASIC
e	.0276	BASIC	0.700	BASIC
e1	.0256	BASIC	0.650	BASIC
e2	.0365	BASIC	0.926	BASIC
e3	.1630	BASIC	4.140	BASIC
L	.0197	.0236	0.500	0.600
M	.1201	1.240	3.050	3.150
N	.0243	.0282	.617	.717
O	.1102	1.142	2.800	2.900
P	.1732	.1772	4.400	4.500
Q	.0607	.0647	1.543	1.643
R	.0266	REF.	0.675	REF.
S	.0266	REF.	0.675	REF.



For footprint and stencil design recommendations, please refer to application note AN-1152 at <http://www.irf.com/technical-info/appnotes/an-1152.pdf>