




# PACKAGE INFORMATION

TOP VIEW



BOTTOM VIEW



DIMENSIONS	Common					
	DIMENSIONS MILLIMETER			DIMENSIONS INCH		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.85	0.90	0.95	0.034	0.036	0.038
A3	0.203 REF.			0.008 REF.		
A1	0.00	0.02	0.05	0.000	0.001	0.002
b	0.20	0.25	0.30	0.008	0.010	0.012
D	3.40	3.50	3.60	0.134	0.138	0.142
D2	2.20	2.25	2.30	0.087	0.089	0.091
D3	1.31	1.36	1.41	0.052	0.054	0.056
D4	0.82	0.87	0.92	0.032	0.034	0.036
E	3.40	3.50	3.60	0.134	0.138	0.142
E2	1.20	1.25	1.30	0.047	0.049	0.051
E3	1.15	1.20	1.25	0.045	0.047	0.049
E4	1.15	1.20	1.25	0.045	0.047	0.049
e	0.50 BSC			0.020 BSC		
L	0.30	0.35	0.40	0.014	0.016	0.018