


TOOL	Symbol	Hit Count	Finished Hole Size	Plated	Hole Type
T1	○	363	0,30mm (11,81mil)	PTH	Round
T2	□	10	0,40mm (15,75mil)	PTH	Round
T3	▽	6	0,90mm (35,43mil)	PTH	Round
T4	⊠	13	1,00mm (39,37mil)	PTH	Round
T5	✡	6	1,10mm (43,31mil)	PTH	Round
T6	◇	15	2,50mm (98,43mil)	PTH	Round
T7	✪	4	5,50mm (216,54mil)	PTH	Round
T8	⊠	4	4,75mm (187,01mil)	NPTH	Round
		421 Total			

COMPANY INFINEON	BOARD TLD5190 IVRG_EVAL_V1.0		NOTES TOL. CONTOUR CUT +0,00/-0,20 s.d.i. TOL. HOLES POSITIONING +/-0,05 s.d.i. TOL. FINISHEDE HOLES DIAMETER +0,1/-0,05 o.i.d.
DATE 21-07-2020	SCALE 1 : 1	DRAWING ZOTTI M. HSE	
FEATURES 4 LAYERS + SOLDER + SILK			
MATERIAL FR4	EXT. BASIC COPPER 35um	PCB THICKNESS 1,0mm	THE ORIGIN OF DRILLING FILE IS REFERS ZERO CARD
DIMENSION 92,0x67,0mmq	INN. BASIC COPPER 35um	TOLLERANCE SEE NOTES	THE MEASURE OF HOLES IS A HOLE FINISHED