


Mechanical dimensions

Electrical diagram



Pinout – bottom view





Dimensions in millimeters

2015/863/UE (RoHS-3) compliant

Electrical features

Inductance N1 @ 10kHz – 100mV	882µH ±30%
Core	CH234060GT14 – Chan Sung Corporation
Copper Wire grade 2, thermal class H	Tenvex or equivalent

REV	APPR DATE	RIF. MOD.	DESCRIPTION OF MODIFICATION	EMITTED	CHECK AND APPROVAL
01	29.05.24		Release	A. Ridolfi	C. Picciani

DESCRIPTION: **PFC inductor 882µH (MG100007000)**

Mod. AQ 05.10

DOCUMENT TYPE	CODE	REVISION	RELASE DATE	PAGE
S.T.	8024.2601.067	01	29.05.24	1of1