

APPROVED: _____


DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-	8719	RELEASED	5/7/08	
A		REDRAWN	5/9/16	AY/NP



RECOMMENDED
CABLE STRIPPING DIM'S







DESCRIPTION	MATERIAL	FINISH
FERRULE	BRASS	GOLD
CONTACT PIN	BRASS	GOLD
RING	BE CU	GOLD
BODY	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD

SPECIFICATIONS:

Electrical:

Frequency Range: DC–6 GHz
Normal Impedance: 50 ohm
Operating voltage: 170 Volts max.
Proof voltage: 500 Volts
VSWR: 1.3 max. @ 1 GHz

Temperature Rating:

Operating temperature: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	5/7/08
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908–687–5000 Fax: 908–687–0214

TITLE
RF CONNECTOR, TYPE MMCX, MALE CRIMP
FOR RG174/U, 316/U, LMR-100, 50 OHM

SIZE	PART NO.	REV.
X	RF12-06-T-02-50-G	A

REF:	SCALE:	SHEET
S00277T	NTS	1 OF 1