


Dimensions



Electrical diagram





Dimensions in millimeters

2015/863/UE (RoHS–3) compliant

Electrical features

Turns ratio N1:N2 @ 10kHz 100mV	1:1
Dielectric strength N1/N2	2000 V – 50 Hz
Core – material	Epcos – B64290L647X38
Copper Wire grade 2, thermal class 180°C	E93551 or equivalent

REV	APPR DATE	RIF. MOD.	DESCRIPTION OF MODIFICATION	EMITTED	CHECK AND APPROVAL
01	26.11.21		Release	A. Ridolfi	C. Picciani

DESCRIPTION: **Common mode choke (MG10000850 CM Choke)**

Mod. AQ 05.09	DOCUMENT TYPE	CODE	REVISION	RELASE DATE	PAGE
	S.T.	8024.3002.048	01	26.11.21	1of1