


Dimensions

PINOUT – BOTTOM VIEW



Electrical diagram





Dimensions in millimeters

2015/863/UE (RoHS–3) compliant

Electrical features

Inductance A–C @ 95kHz 100mV	58.5 ÷ 71.5 µH
Dielectric strength N1+N2+N4/N3	3000 V – 50 Hz
Dielectric strength N1+N2+N3+N4/core	500 V – 50 Hz
Core – material	DMEGC – DMR95
Triple Insulated Litz Wire, RUPALIT Safety VB155	VDE n.122034

REV	APPR DATE	RIF. MOD.	DESCRIPTION OF MODIFICATION	EMITTED	CHECK AND APPROVAL
01	26.11.21		Release	A. Ridolfi	C. Picciani

DESCRIPTION: **Main Transformer PQ35/23 choke PQ35/28 (TF100002802)**

Mod. AQ 05.09

DOCUMENT TYPE	CODE	REVISION	RELASE DATE	PAGE
S.T.	8065.1104.002	01	26.11.21	1of1