

## Electrical diagram




## Drawing




2011/65/UE (RoHS-2) Compliant

Dimensions in millimeters

## Electrical characteristics

| | |
|---|---|
| Inductance 1-2 @ 10kHz - 100mV | 134 ÷ 148.5 µH |
| Dielectric strength 1+2/A÷H | 3000V - 50Hz |
| Dielectric strength A÷H/core | 300V - 50Hz |
| | |
| | |

| REV | APPR DATE | REF. MOD. | DESCRIPTION OF MODIFICATION | EDITING | CHECKING AND APPROVAL |
|---|---|---|---|---|---|
| 01 | 24.05.18 | | Emissione | C. Picciani | D. Di Giorgio |

DESCRIPTION: **Main Transformer PQI 35/23 (TF10000730 1600W V02)**

Mod. AQ 05.09

| DOCUMENT TYPE | P/N | REVISION | RELEASE DATE | PAGE |
|---|---|---|---|---|
| S.T. | 8065.1104.001 | 01 | 24.05.18 | 1of1 |