



| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN. | NOM. | MAX. |
| A | - | - | 1 |
| A1 | 0.18 | - | - |
| D | 11 BSC. | | |
| E | 8 BSC. | | |
| Øb | 0.33 | - | 0.43 |
| eD/eE | 0.8 BSC. | | |
| SD/SE | 0.4 BSC. | | |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing methods per ASME Y14.5M-1994.