





Bottom view




| SYMBOL | DIMENSIONS | | |
|---|---|---|---|
| | MIN. | NOM. | MAX. |
| A | - | - | 1.4 |
| A1 | 0.17 | - | - |
| A2 | 0.98 | - | 1.15 |
| D | 13 BSC | | |
| E | 11 BSC | | |
| Øb | 0.35 | 0.4 | 0.45 |
| eE | 0.8 BSC | | |
| eD | 0.8 BSC | | |
| SD / SE | 0.4 BSC | | |

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Dimensioning and tolerancing methods per ASME Y14.5M-1994.