


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	3.35
A1	0.05	-	0.4
b	0.32	0.37	0.42
c	0.11	-	0.23
D	23.9 BSC		
D1	20 BSC		
e	0.8 BSC		
E	17.9 BSC		
E1	14 BSC		
θ	0°	-	8°
L	0.73	0.88	1.03

1) Dimensions D1 and E1 do not include mold protrusion.allowable protrusion is 0.25mm per side.
2) Dimension b does not include damber protrusion. the dambar protrusion(s) shall not cause the lead width to exceed b maximum by more than 0.08mm.
All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]