


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.20
D		6.50 BSC	
E		6.50 BSC	
D1		4.50 BSC	
E1		5.50 BSC	
D2		1.24 BSC	
E2		1.24 BSC	
D3		5.65 BSC	
E3		5.65 BSC	
b		0.25 BSC	
b1		0.35 BSC	
L		0.45 BSC	
f		0.20 BSC	
eD		0.50 BSC	
eE		0.50 BSC	

All dimensions are in units mm
The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]
Drawing according to ISO 8015, general tolerances ISO 2768-mK